



Certificate of Conformity

VWR FILTER TIPS RACKED STERILE

VWR International certifies that the products comply in every respect with the relevant particular specifications and/or drawings and/or relevant standards and regulations in force, mentioned in this document.

VWR International certifie que les produits sont conformes à tous égards aux spécifications particulières appropriées et / ou dessins, normes et règlements en vigueur, mentionnées dans le présent document

VWR International bestätigt, dass das Produkte allen zutreffenden Spezifikations- und/oder Zeichnungs- und/oder Standardanforderungen sowie den im Dokument aufgeführten gültigen Vorschriften entspricht.

Cat. No.	Tip style	Volume (µl)	Length (mm)	Compatibility	Packed	Pk
613-0752	Wide orifice	100 - 1000	88.90	AF9	6 racks, 96 each	576
613-0753	Aerosol-barrier	100 - 1200	88.90	K	6 racks, 96 each	576
732-0516	UltraFine™, graduated	0.1 - 10	31.42	AF1	12 racks, 96 each	1.15 2
732-0519	Bevel Point™, graduated	0.5 - 10	44.83	AF2	10 racks, 96 each	960
732-0520	Bevel Point™	1 - 50	49.66	AF4	10 racks, 96 each	960
732-0523	Bevel Point™	1 - 100	49.66	AF5	10 racks, 96 each	960
732-0525	Bevel Point™	1 - 40	49.66	AF3	5 racks, 192 each	960
732-0528	Bevel Point™	1 - 40	49.66	AF3	10 racks, 96 each	960
732-0530	Bevel Point™	1 - 160	49.66	AF6	10 racks, 96 each	960
732-0534	UltraFine™	100 - 1000	88.90	AF9	6 racks, 96 each	576
732-0537	Bevel Point™	1 - 300	52.07	AF8	10 racks, 96 each	960
732-0541	UltraFine™	1 - 200	52.07	AF7	10 racks, 96 each	960
732-0543	UltraFine™, extended	0.1 - 10	38.10	AF1	10 racks, 96 each	960
732-0544	Bevel Point™, wide orifice	1 - 200	49.66	AF7	10 racks, 96 each	960



Certificate of Conformity

Cat. No.	Tip style	Volume (µl)	Length (mm)	Compatibility	Packed	Pk
732-0573	Bevel Point™	1 - 160	49.66	AF6	5 racks, 192 each	960
732-0610	UltraFine™, extended	1 - 200	83.82	AF7	6 racks, 96 each	576
732-0611	UltraFine™, extended	1 - 300	71.12	AF8	6 racks, 96 each	576
732-0799	Rainin® LTS™ style	0.1 - 20	48.26	AF13	10 racks, 96 each	960
732-0800	Rainin® LTS™ style	1 - 200	51.31	AF11	10 racks, 96 each	960
732-0801	Rainin® LTS™ style	100 - 1000	88.90	AF12	6 racks, 96 each	576
732-1100	Micro	0.1 - 30	38.10	AF1	10 racks, 96 each	960
732-1101	UltraFine™, graduated	0.5 - 10	49.66	AF16	10 racks, 96 each	960
732-1102	Bevel Point™, graduated	1 - 100	49.66	AF5	10 racks, 96 each	960
732-1103	Standard	1 - 100	49.66	AF5	10 racks, 96 each	960
732-1105	UltraFine™, FlexTop™, graduated	1 - 50	49.66	AF4	10 racks, 96 each	960
732-1106	UltraFine™, FlexTop™	100 - 1000	75.95	AF9	6 racks, 96 each	576
732-1107	UltraFine™, extended	1 - 100	83.82	AF5	6 racks, 96 each	576
732-2894	Sartorius® type	1250	88.90	-	6 racks, 96 each	576
732-2898	Rainin® LTS™ style, low retention	1 - 300	61	AF8	10 racks, 96 each	960



Certificate of Conformity

Other Characteristics:

- All the tips are made of high quality 100% pure virgin medical grade PP.
- Made in the highest quality moulds, these tips can be used whenever the work demands a higher standard.
- Resins are pre-tested for metal contamination.
- A wider seal assures that tips will seal easily and consistently without leaking on old as well as new pipettes
- Certified RNase-/DNase-free

Pyrogens:

Certified testing is performed lot by lot. These tests include Nuclease (Rnase,Dnase) and Endotoxin (pyrogen). Certificates are on file at the production facility.

Product Sterilization:

Those products designated as Sterile are irradiated by gamma radiation. The validated dosage level for these products is in a range between 15.2 - 32.0kGy.

Certified as sterile with a sterility assurance level (SAL) of 10^{-6} and a sterile shelf life of three years.

Disclaimer: VWR wants to state that this declaration will not discharge the user from his obligation to ensure the product is suitable for the intended use. - If there is any doubt ask us.

Date of issue: **December 2016**