



Technical Data Sheet



Dimensions (Unit: mm)





VWR® 850ml Cell Attachment Treated Tissue Culture Flasks

Description: 850ML, Treated for Increased Cell Attachment, w/plug seal cap, Sterilized 850ML, Treated for Increased Cell Attachment, w/vent cap, Sterilized

Purpose: An innovative surface rendering it more hydrophilic and increasing surface stability

Materials

Flask: GPPS (General polystyrene) Color: Clear

Cap: HDPE(High Density Polyethylene) Color: Purple 259 Membrane: 0.22µm Hydrophobic PP (Only use for Vented Cap)

Features

• Temperature: -20°C~+50°C

• Sterilation: sterilized by gamma irradiation SAL10⁻⁶(ISO11137)

· Latex Statement: this product is latex free

• Non-pyrogenic

• Bulk packed in zip-Lock bag

· Autoclavability: No

• Working volume: 800 ml • Growth area: 300.0 cm2

· Every product is printed with a batch number for traceability

• Shelf Life: 3 years after month of production



VWR® 850ml Cell Attachment Treated Tissue Culture Flasks

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Bag	Qty/Pk	Qty/Case
734-2812	10861-652	850ML, Treated for Increased Cell Attachment, w/plug seal cap, Sterilized	Yes	3	9	18
734-2813	10861-654	850ML, Treated for Increased Cell Attachment, w/vent cap, Sterilized	Yes	3	9	18

Cautionary Stements

Ximus. Ximporem fugiaerae vel is dolluptaepta volupti dolore, undam, quatur, ationsequo que aliqui ne pe exeribust, omnimpel ipsamus que labo. Lo et mint estrum, officatio te doluptate coresciis moloritio que conseque quis sit atus, eume nistem quas moloria qui si aut qui tem estis aut liasimiligni



1.800.932.5000 | vwr.com


Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | VWR. the VWR logo and variations on the foregoing are registered (b) or unregistered trademarks and service marks, of VWR International, LLC. and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vwr.com to view our privacy policy, trademark owners and additional disclaimers. ©2015 VWR International, LLC. All rights reserved.



Technical Data Sheet



3:Dimensions (Unit: mm)



VWR® 600ml Cell Attachment Treated Tissue Culture Flasks

Description: 600ML, Treated for Increased Cell Attachment, w/plug seal cap, Sterilized 600ML, Treated for Increased Cell Attachment, w/vent cap, Sterilized

Purpose: An innovative surface rendering it more hydrophilic and increasing surface stability

Materials

Flask: GPPS (General polystyrene) Color: Clear

Cap: HDPE(High Density Polyethylene) Color: Purple 259 Membrane: 0.22µm Hydrophobic PP (Only use for Vented Cap)

Features

• Temperature: -20°C~+50°C

• Sterilation: sterilized by gamma irradiation SAL10⁻⁶(ISO11137)

· Latex Statement: this product is latex free

• Non-pyrogenic

• Bulk packed in zip-Lock bag

· Autoclavability: No

Working volume: 400 mlGrowth area: 182.0 cm2

• Every product is printed with a batch number for traceability

• Shelf Life: 3 years after month of production



VWR® 600ml Cell Attachment Treated Tissue Culture Flasks

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Bag	Qty/Pk	Qty/Case
734-2810	10861-648	600ML, Treated for Increased Cell Attachment, w/plug seal cap, Sterilized	Yes	5	20	40
734-2811	10861-650	600ML, Treated for Increased Cell Attachment, w/vent cap, Sterilized	Yes	5	20	40

Cautionary Stements

Ximus. Ximporem fugiaerae vel is dolluptaepta volupti dolore, undam, quatur, ationsequo que aliqui ne pe exeribust, omnimpel ipsamus que labo. Lo et mint estrum, officatio te doluptate coresciis moloritio que conseque quis sit atus, eume nistem quas moloria qui si aut qui tem estis aut liasimiligni



1.800.932.5000 | vwr.com

Prices and product details are current when published; subject to change without notice. | Certain products may be limited by federal, state, provincial, or local regulations. | VWR makes no claims or warranties concerning sustainable/green products are the sole claims of the manufacturer and not those of VWR International, LLC. All prices are in US dollars unless otherwise noted. Offers valid in US and Canada, void where prohibited by law or company policy, while supplies last. | VWR. the VWR logo and variations on the foregoing are registered (b) or unregistered trademarks and service marks, of VWR International, LLC. and its related companies. All other marks referenced are registered by their respective owner(s). | Visit vwr.com to view our privacy policy, trademark owners and additional disclaimers. ©2015 VWR International, LLC. All rights reserved.