


Dimensions ( Unit: mm)



VWR® 25mL Treated Tissue Culture Flasks

Description: 25ML, Treated, w/plug seal cap, Sterilized  
25ML, Treated, w/vent cap, Sterilized

Purpose: For use in applications where cell attachment is desired

Materials

Flask: GPPS ( General polystyrene ) Color: Clear


Cap: HDPE( High Density Polyethylene ) Color: Purple 259

Membrane: 0.22µm Hydrophobic PP (Only use for Vented Cap)



- Features
- Temperature: -20°C~+50°C
  - Sterilation: sterilized by gamma irradiation SAL10<sup>6</sup>(ISO11137)
  - Non-pyrogenic
  - Bulk packed in zip-Lock bag
  - Autoclavability: No
  - Working volume: 20 ml
  - Growth area: 12.5 cm2
  - Every product is printed with a batch number for traceability
  - Shelf Life: 3 years after month of production

VWR® 25ml Treated Tissue Culture Flasks

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Bag	Qty/Pk	Qty/Case
734-2310	10062-870	25ML Tissue Culture Flask, Treated, w/plug seal cap, Sterilized	Yes	10	50	200
734-2309	10062-868	25ML Tissue Culture Flask, Treated, w/vent cap, Sterilized	Yes	10	50	200



Dimensions ( Unit: mm)



VWR® 50mL Treated Tissue Culture Flasks

Description: 50ML, Treated, w/plug seal cap, Sterilized  
50ML, Treated, w/vent cap, Sterilized

Purpose: For use in applications where cell attachment is desired

Materials


- Flask: GPPS ( General polystyrene ) Color: Clear  
Cap: HDPE( High Density Polyethylene ) Color: Purple 259  
Membrane: 0.22µm Hydrophobic PP (Only use for Vented Cap)

Features

- Temperature: -20°C~+50°C
- Sterilation: sterilized by gamma irradiation SAL10<sup>6</sup>(ISO11137)
- Non-pyrogenic
- Bulk packed in zip-Lock bag
- Autoclavability: No
- Working volume: 40 ml
- Growth area: 25.0 cm<sup>2</sup>
- Every product is printed with a batch number for traceability
- Shelf Life: 3 years after month of production

VWR® 50ml Treated Tissue Culture Flasks

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Bag	Qty/Pk	Qty/Case
734-2312	10062-874	50ML Tissue Culture Flask, Treated, w/plug seal cap, Sterilized	Yes	10	50	200
734-2311	10062-872	50ML Tissue Culture Flask, Treated, w/vent cap, Sterilized	Yes	10	50	200



VWR® 250mL Treated Tissue Culture Flasks

Description: 250ML, Treated, w/plug seal cap, Sterilized  
250ML, Treated, w/vent cap, Sterilized


Purpose: For use in applications where cell attachment is desired

Materials

- Flask: GPPS ( General polystyrene ) Color: Clear
- Cap: HDPE( High Density Polyethylene ) Color: Purple 259
- Membrane: 0.22µm Hydrophobic PP (Only use for Vented Cap)

Features

- Temperature: -20°C~+50°C
- Sterilation: sterilized by gamma irradiation SAL10<sup>6</sup>(ISO11137)
- Non-pyrogenic
- Bulk packed in zip-Lock bag
- Autoclavability: No
- Working volume: 175 ml
- Growth area: 75.0 cm2
- Every product is printed with a batch number for traceability
- Shelf Life: 3 years after month of production



VWR® 250ml Treated Tissue Culture Flasks

VWR EU Cat. No.	VWR NA Cat. No.	Description	Sterile	Qty/Bag	Qty/Pk	Qty/Case
734-2314	10062-862	250ML Tissue Culture Flask, Treated, w/plug seal cap, Sterilized	Yes	5	25	100
734-2313	10062-860	250ML Tissue Culture Flask, Treated, w/vent cap, Sterilized	Yes	5	25	100